



CO-AX Carbon Monoxide Sensor EN 50379 Compliant for Stack Gases






PATENTED

15 to 90

10 to 47



PERFORMANCE	Sensitivity Response time Zero current Resolution Range Linearity Overgas limit	nA/ppm in 400ppm CO t ₉₀ (s) from zero to 400ppm CO ppm equivalent in zero air RMS noise (ppm equivalent) ppm CO limit of performance warranty ppm error at full scale, linear at zero and 800ppm CO maximum ppm for stable response to gas pulse	55 to 100 < 30 < ± 3 < 0.5 2,000 < ± 40 4,000
LIFETIME	Zero drift Sensitivity drift Operating life	ppm equivalent change/year in lab air % change/year in lab air, monthly test months until 80% original signal (24 month warranted)	<0.2 <6 > 24
ENVIRONMENTAL	Sensitivity @ 0°C	C% (output @ -20°C/output @ 20°C) @ 400ppm CO C% (output @ 0°C/output @ 20°C) @ 400ppm CO C% (output @ 40°C/output @ 20°C) @ 400ppm CO ppm equivalent change from 20°C ppm equivalent change from 20°C ppm equivalent change from 20°C	55 to 75 75 to 90 106 to 120 < 0 to 4 < 0 to 3 < 0 to -6
CROSS SENSITIVITY	Filter capacity Filter capacity Filter capacity Filter capacity Filter capacity H ₂ sensitivity H ₂ sensitivity H ₂ sensitivity NO ₂ sensitivity Cl ₂ sensitivity NO sensitivity SO ₂ sensitivity C ₂ H ₄ sensitivity NH ₃ sensitivity	ppm-hours H ₂ S ppm-hours NO ₂ ppm-hours NO ppm-hours SO ₂ % measured gas @ 900ppm H ₂ in 900ppm CO @ 10°C % measured gas @ 900ppm H ₂ in 900ppm CO @ 20°C % measured gas @ 900ppm H ₂ in 900ppm CO @ 30°C % measured gas @ 10ppm NO ₂ % measured gas @ 10ppm Cl ₂ % measured gas @ 500ppm NO % measured gas @ 20ppm SO ₂ % measured gas @ 400ppm C ₂ H ₄ % measured gas @ 20ppm NH ₃	< 4
KEY SPECIFICATIONS	Temperature range Pressure range	°C kPa	-30 to 50 80 to 120

Important. The CO-AX must be operated with a 0 Volt bias between Reference & Working electrodes. Failure to comply with this requirement will result in a loss of its low Hydrogen cross sensitivity performance.

% rh continuous

 Ω (recommended)



Humidity range

Storage period

Load resistor

Weight

At the end of the product's life, do not dispose of any electronic sensor, component or instrument in the domestic waste, but contact the instrument manufacturer, Alphasense or its distributor for disposal instructions.

months @ 0 to 20°C (stored in sealed pot)

NOTE: all sensors are tested at ambient environmental conditions, with 10 ohm load resistor, unless otherwise stated. As applications of use are outside our control, the information provided is given without legal responsibility. Customers should test under their own conditions, to ensure that the sensors are suitable for their own requirements.





CO-AX Performance Data

Figure 2 CO Sensitivity Temperature Dependence




Figure 2 shows the variation in sensitivity caused by changes in temperature.

This data is taken from a typical batch of sensors.

Figure 3 Hydrogen Sensitivity Temperature Dependence




Figure 3 shows the strong temperature dependence of the CO-AX to hydrogen. Since hydrogen sensitivity is less than 4% at 20°C, hydrogen interference can practically be ignored at low temperatures. However, at 50°C hydrogen interference is 14%.

This data is taken from a typical batch of sensors. The mean and ±95% confidence intervals are shown.

Figure 4 Hydrogen Cross Sensitivity at 30^oC




Figure 4 shows hydrogen sensitivity for a typical batch of eight CO-AX sensors at 30°C following EN50379. All sensors show less than 5% cross sensitivity when 500ppm hydrogen is added to 950ppm carbon monoxide. t₉₀ is less than 45 seconds.

For further information on the performance of this sensor, on other sensors in the range or any other subject, please contact Alphasense Ltd. For detailed application notes go to "www.alphasense.com".

In the interest of continued product improvement, we reserve the right to change design features and specifications without prior notification. The data contained in this document is for guidance only. Alphasense Ltd accepts no liability for any consequential losses, injury or damage resulting from the use of this document or the information contained within (@ALPHASENSE LTD) Doc. Ref. COAX/JUL14